




V500 PC-Free Document Camera

PC-FREE | HD | HIGH SPEED| BUILT-IN SOFTWARE | PLUG&PLAY | e-CLASSROOM | e-OFFICE


FOR CONFERENCE MEETING
FOR DISTANCE LEARNING

1 Button Panel




2 CONNECT TO PC

- 1 CONNECT V500 WITH PC VIA USB CABLE
- 2 PLUG IN POWER INPUT
- 3 LAUNCH SOFTWARE




3 DUAL-MODE





ONLINE MODE (CONNECT WITH PC)

- Install Nugens Visualizer Software in PC
- Connect to PC via USB Cable
- Plug in AC Adapter and Press ON
- Launch software, scanning or recording or displaying.
- Scanned / Recorded files will be saved in local folder of PC.



OFFLINE MODE (PC-FREE)

- Insert Mouse's USB to V500
- Connect Projector / TV's HDMI to V500
(Or Connect via VGA Cable to V500's VGA-OUT)
- Power ON V500.
- Press to Zoom-In or Zoom-Out.





HDMI
/ VGA

Connect




4 V500 Software Installation

Please visit www.nugenstech.com to download Nugens Visualizer Software and install it.



5 Intro of Nugens Visualizer Software
















Offline Mode: Use HDMI / VGA cable to connect a TV or a Projector












Online Mode: Connect PC via USB Cable to use Nugens Visualizer Software



Functions:

Icon	Description
	Focus: Press to focus.
	Magnifier: Zoom in on specific area.
	Resolution: Dimensions are 800x600, 1280x720, 1280x960, 1920x1080, 2048x1536, 2592x1944, 3264x2448.
	Zoom-in: Zoom in entire page.
	Zoom-out: Zoom out entire page.
	Rotate: Rotate entire page 90 degrees.
	Freeze: Freeze entire page; it can be zoom in or rotate when in freeze. Press it again to unfreeze.
	 <p>Color-adjusting: You can adjust the Contrast, Brightness and Saturation.</p>
	Self-adapting: Press to adjust to the best aspect ratio.
	Automatic-edging: Auto Edge.
	 <p>Snap: Customize capture areas, such as Screen Capture, Partial Screen Capture, Timing Capture, Screen Capture to Clipboard, Black and White Capture, Grayscale Capture.</p>
	Video-Recording: Full screen recording or record part of the screen as 1024x768, 1080x720, 800x600, 640x480.
	Optical Character Recognition (OCR): Supports multiple language recognition, and export to PDF, Word, Excel and Text.

Icon	Description
	Move: Move the image.
	Pencil: Draw a free-form line with the selected line width.
	Thickness: Select the preferred outline for Pencil.
	Color: Select the preferred color for Pencil.
	Transparency: Adjust the transparency of Pencil, also able to use as highlighter.
	Text: Insert text into the picture.
	Shape: Insert Shape to highlight on picture. There are Straight Lines, Circle, Oval, Triangle and Rectangle.
	Erase: Erase any annotation that made by Pencil or Shape.
	Clear: Clear all marks that made by Pencil or Shape.

Timing Capture:

By using this function, you can use visualizer to capture frame-by-frame animations. You may set the numbers of frames, change frame in one second. If you want to capture a book content to become an E-book, you may use this function too.

1.Interval Time: Set the number for intervals you want.

2.Capture Pages: Set the number for pages you want.

Interval Time **S**


Capture Pages **P**

Confirm
Cancel

OCR:

By using this function, you can capture book or document and convert them into texts, also, you can output it as PDF, Word, Excel or Text file.

Note: If there were too many photos or designed texts, it will affect the recognition.



6 Nugens CamSwitcher Software

Please visit www.nugentech.com to download Nugens CamSwitcher Preview software and install it.

With Nugens CamSwitcher Preview, you are able to display HD preview with user friendly design. You are able to select resolutions, brightness, and other settings.

